

# Power Distribution Unit

## PDU UK, basic version

Power		Pin patterns			Dimensions		Model No.
No. of phases	Phase current A	Input	Outputs UK connector	Outputs C19	PDU length mm	Minimum enclosure height mm	
1	13	UK	6	–	440	600	<b>7955.510</b>
1	13	UK	8	–	535	800	<b>7955.511</b>
1	13	UK	10	–	640	800	<b>7955.512</b>
1	13	UK	12	–	745	1000	<b>7955.513</b>

## PDU UK, metered version

Power		Pin patterns			Dimensions		Model No.
No. of phases	Phase current A	Input	Outputs UK connector	Outputs C19	PDU length mm	Minimum enclosure height mm	
1	13	UK	16	–	1210	1400	<b>7955.520</b>
1	16	CEE	20	4	1695	2000	<b>7955.521</b>
1	32	CEE	20	4	1955	2200	<b>7955.522</b>

## PDU UK, switched version

Power		Pin patterns			Dimensions		Model No.
No. of phases	Phase current A	Input	Outputs UK connector	Outputs C19	PDU length mm	Minimum enclosure height mm	
1	13	UK	16	–	1210	1400	<b>7955.530</b>
1	16	CEE	16	4	1380	1800	<b>7955.531</b>
1	32	CEE	16	4	1520	1800	<b>7955.532</b>

## PDU UK, managed version

Power		Pin patterns			Dimensions		Model No.
No. of phases	Phase current A	Input	Outputs UK connector	Outputs C19	PDU length mm	Minimum enclosure height mm	
1	13	UK	16	–	1210	1400	<b>7955.540</b>
1	16	CEE	16	4	1380	1800	<b>7955.541</b>
1	32	CEE	16	4	1525	1800	<b>7955.542</b>

## Slave PDU UK, managed version

Power		Pin patterns			Dimensions		Model No.
No. of phases	Phase current A	Input	Outputs UK connector	Outputs C19	PDU length mm	Minimum enclosure height mm	
1	13	UK	16	–	1210	1400	<b>7955.940</b>
1	16	CEE	16	4	1380	1800	<b>7955.941</b>
1	32	CEE	16	4	1525	1800	<b>7955.942</b>

## PDU accessories

	Packs of	Model No.	Page
Covers for C13 slot, lockable	10 pc(s).	<b>7955.010</b>	
Covers for C19 slot, lockable	10 pc(s).	<b>7955.015</b>	
Connector, universal lock for C14/C20 connector	20 pc(s).	<b>7955.020</b>	
Connection cable D/C19, 1.8 m	1 pc(s).	7200.216	457
Connection cable C19/C20, 1.8 m	1 pc(s).	7200.217	457

## CMC III sensors (max. 4 sensors per PDU)

CMC III/PDU sensor type	Packs of	Model No.	Page
Temperature sensor	1 pc(s).	7030.110	454
Temperature/humidity sensor (combi-sensor)	1 pc(s).	7030.111	454
Infrared access sensor	1 pc(s).	7030.120	454
Vandalism sensor	1 pc(s).	7030.130	454
CMC III CAN bus connection cable RJ 45, length 0.5 – 10 m	1 pc(s).	see page 457	