

Doors/locks

Door, internal



Sheet steel wiring plan pockets

for TS, SE, CM, TP pedestal, PC

For fastening to tubular door frames at any height.

Colour:

– RAL 7035

Supply includes:

– Assembly screws



D = 90 mm

To fit door width mm	Clearance openings mm		Model No.
	W	H	
400	255	210	4114.000
500	355	210	4115.000
600	455	210	4116.000
800	655	210	4118.000
900	755	210	4123.000
1000	855	210	4124.000

D = 35 mm

To fit door width mm	Clearance openings mm		Model No.
	W	H	
500	355	210	4115.500
600	455	210	4116.500
800	655	210	4118.500



Door stay

To secure the door in the open position.

Supply includes:

– Assembly parts

For	Mounting	Packs of	Model No.
TS, SE, TP universal console, PC	Bottom	5 pc(s).	4583.000
CM, TP	Top	2 pc(s).	2519.200
AE (except 1032.500 and 1035.500) and all AE stainless steel enclosures ¹⁾	Top	5 pc(s).	2519.000

¹⁾ With AE stainless steel, only in conjunction with perforated mounting strips, see page 576



Door stay for escape routes

for TS, SE, PC

In case of an emergency, conventional door stays can block the escape route. This stay is actuated automatically in the event of pressure, releasing the door in both directions. In conjunction with 180° hinges, this ensures that no escape routes are blocked by open doors in the event of an emergency.

Supply includes:

– Assembly parts

Packs of	Model No.
1 pc(s).	4583.500

+ Accessories:

– 180° hinge, see page 574

180° hinge

