



**System accessories** Page 507 **482.6 mm (19") installation accessories** Page 678 **482.6 mm (19") climate control** Page 307

### Material and surface finish:

- Enclosure frame: Sheet steel, 1.5 mm, dipcoat-primed
- Roof: Sheet steel, 1.5 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Front frame: Extruded aluminium section with die-cast corner pieces, powder-coated

- Rear door: Sheet steel, 2 mm, dipcoat-primed, powder-coated on the outside, textured paint
- Gland plates: Sheet steel, 1.5 mm, zinc-plated
- Adaptor sections: Aluminium

### Colour:

- RAL 7035

### Supply includes:

- Enclosure frame
- Front frame (r/h hinge, opening angle 130°, held on the left via mechanical snap fasteners)
- Rear door (r/h hinge, may be swapped to opposite side)
- Roof
- Adaptor sections, 482.6 mm (19") attachment level
- Gland plates

### Approvals:

- UL
- cUL

### Technical details:

Available on the Internet

## Electronic enclosures

Units U	Packs of	33	33	42	42	Page
Width mm		600	600	600	600	
Height mm		1600	1600	2000	2000	
Depth mm		600	800	600	800	
Model No.	1 pc(s).	<b>8410.510</b>	<b>8418.510</b>	<b>8430.510</b>	<b>8438.510</b>	
Door(s)		1	1	1	1	

### Accessories

Side panels, screw-fastened, sheet steel	2 pc(s).	8166.235	8168.235	8106.235	8108.235	534
Flex-Block corner pieces, 100 mm	1 set(s)	8100.000	8100.000	8100.000	8100.000	511
Flex-Block trim panels, 100 mm, sealed, for width	1 set(s)	8100.600	8100.600	8100.600	8100.600	511
Flex-Block trim panels, 100 mm, sealed, for depth	1 set(s)	8100.600	8100.800	8100.600	8100.800	511
Flex-Block corner pieces, 200 mm	1 set(s)	8200.000	8200.000	8200.000	8200.000	511
Flex-Block trim panels, 200 mm, sealed, for width	1 set(s)	8200.600	8200.600	8200.600	8200.600	511
Flex-Block trim panels, 200 mm, sealed, for depth	1 set(s)	8200.600	8200.800	8200.600	8200.800	511
Base/plinth components, front and rear, 100 mm	1 set(s)	8601.600	8601.600	8601.600	8601.600	513
Base/plinth trim panels, side, 100 mm	1 set(s)	8601.060	8601.080	8601.060	8601.080	514
Base/plinth components, front and rear, 200 mm	1 set(s)	8602.600	8602.600	8602.600	8602.600	513
Base/plinth trim panels, side, 200 mm	1 set(s)	8602.060	8602.080	8602.060	8602.080	514
Levelling feet	4 pc(s).	4612.000	4612.000	4612.000	4612.000	520
Cable clamp rails	2 pc(s).	4191.000	4191.000	4191.000	4191.000	665
C rails 30/15	6 pc(s).	4944.000	4944.000	4944.000	4944.000	612
Baying system		from page	from page	from page	from page	542
Section for cable entry, rear	1 set(s)	8802.065	8802.065	8802.065	8802.065	652
Adaptor sections, 482.6 mm (19")	2 pc(s).	8613.360	8613.360	8613.300	8613.300	684
LED system light	1 pc(s).	4140.830	4140.830	4140.830	4140.830	637
Compact light	1 pc(s).	4140.010	4140.010	4140.010	4140.010	636
Lock systems		from page	from page	from page	from page	561