

Socket strip

Earthing-pin, with plastic housing

Robust 8-way earthing-pin socket strip in a plastic housing. The strip may be mounted vertically on the enclosure frame or in the 482.6 mm (19") section. 2.5 U are required for 482.6 mm (19") installation. The earthing-pin inserts are arranged at an angle of 45° so that angular connectors are also easily used. The connection cable is attached to a terminal connection (behind a removable cover) in the socket strip. The socket strip has a terminal for an external earthing connection.

Technical specifications:

- Connector type F (CEE 7/4)
- Rated operating voltage: 230 V
- Rated current: 16 A
- Connection cable: Type H05VV-F3G1.5 (black) with wire end ferrules
- Length: 2 m
- Dimensions:
W x H x D: 483 x 74 x 45 mm

Socket strip	Model No.
8-way, earthing-pin	7000.630

Supply includes:

- 1 socket strip
- Assembly parts

Material:

- Plastic (grey/black)

Approvals:

- CE
- RoHS



Socket strip

Earthing-pin, with ammeter

The socket strip with ammeter measures the active power of the connected equipment. The 482.6 mm (19") long socket strip may optionally be mounted on the 482.6 mm (19") mounting angles, on the 482.6 mm (19") mounting frame, on the enclosure frame or in the rear section of wall-mounted distributors. The installation bracket may be mounted in four different positions for variable mounting. Without additional mounting accessories, the socket strip may be inserted into all sections with a 25 mm pitch pattern.

Technical specifications:

- Rated operating voltage: 250 V
- Rated current: 16 A
- Connection cable: Type H05VV-F3G1.5 (black) with wire end ferrules
- Length: 3 m
- Dimensions:
W x H x D: 480 x 45 x 50 mm

Material:

- Aluminium section: Natural anodised
- Socket inserts: Polycarbonate

Display colour:

- Blue, luminescent

Supply includes:

- 1 socket strip
- 2 installation brackets
- Assembly parts
- 3 m connection cable with wire end ferrules

Approvals:

- CE
- RoHS



Version	No. of sockets	Attachment			Length mm	Mounting dimensions mm ¹⁾	Model No.
		Frame	Wall-mounted distributor, horizontal	482.6 mm (19") level			
IEC 320/CEE 7/4	7	■	■	■	482.6	464.1	7240.300

¹⁾ Variable attachment distance within a range of 25 mm, the dimension given is hole centre – hole centre of the mounting bracket